

Swagelok North Carolina | East Tennessee Quick Reference Guide

FILTERS

[Coalescing Filters](#)
[High-Purity Filters](#)
[Particulate Filters: Inline and Tee Type](#)



FITTINGS

[Swagelok® Tube Fittings \(1/16" — 2"\)](#)
[B Type VCO® L-Ring Face Seal Fittings](#)
[Dielectric Fittings](#)
[Flange to Swagelok Tube Fitting](#)
[PFA Fine Thread Flare Fittings](#)
[Pipe Fittings](#)
[Vacuum Fittings](#)
[VCO® O-Ring Face Seal](#)
[VCR® Metal Gasket Face Seal](#)
[Weld Fittings](#)



HOSES AND FLEXIBLE TUBING

[313 SS Core Hoses, SS Braid](#)
[Hose and Flexible Tubing End Connections](#)
[Nylon Core Hose, Fiber Braid Reinforced](#)
[PFA Core Hose, 302 SS Braid Reinforced](#)
[PFA Flexible Tubing](#)
[Polyethylene Core, Fiber Braid Reinforced](#)
[PTFE Core Hose, Convolutd or Smooth Bore](#)
[Rubber Core Hose, Rayon Fiber Reinforced](#)
[Vacuum Flexible Tubing Convolutd 316 SS](#)
[Vinyl Flexible Tubing](#)
[Accessories](#)



LEAK DETECTORS, LUBRICANTS, SEALANTS

[Heat Exchanger Tube Plugs](#)
[Lubricants \(Goop®\)](#)
[Sealants \(PTFE Tape, SWAK®, PTFE-Free\)](#)
[Snoop® Liquid Leak Detector](#)



MEASUREMENT DEVICES

[Flow Sensors](#)
[Pressure Gauges](#)
[Pressure Transducers](#)
[Thermometers](#)
[Thermowells](#)
[Variable Area Flowmeters](#)



MINIATURE MODULAR SYSTEMS

[Analytical, Modular Platform Components](#)
[Ultrahigh-Purity, Integrated Gas Components](#)



PRE-ENGINEERED SUBSYSTEMS

[Calibration and Switching Modules](#)
[Fast Loop Modules](#)
[Field Station Modules](#)
[Fluid Distribution Headers](#)
[Sample Probe Modules](#)



QUICK CONNECTS

[Full-Flow](#)
[Instrumentation](#)
[Miniature](#)
[PTFE-Sealed](#)



REGULATORS

[Back-Pressure, Dome-Loaded](#)
[Back-Pressure, Spring-Loaded](#)
[Pressure-Reducing, Dome-Loaded](#)
[Pressure-Reducing, Spring-Loaded](#)
[Specialty](#)



SAMPLE CYLINDERS

[Miniature Sample Cylinders](#)
[Single & Double ended Cylinders](#)



TOOLS AND ACCESSORIES

[Tube Benders](#)
[Tube Cutter](#)
[Deburring Tool](#)
[Hydraulic Swaging Units](#)
[Inspection Gauges](#)
[Lubricants](#)
[Orbital Welding System](#)
[Sealants](#)
[Wrenches](#)



TUBING AND TUBE SUPPORTS

[304 304L and 316 316L Seamless](#)
[304/304L Welded](#)
[316L Titanium Alloyed](#)
[Insulated Tubing](#)
[Jacketed Tubing](#)
[Multijacketed Tubing](#)
[Support Systems](#)



VALVES AND MANIFOLD VALVES

[Ball Valves](#)
[Bellows-Sealed Valves](#)
[Bleed and Purge Valves](#)
[Check Valves](#)
[Diaphragm-Sealed](#)
[Excess Flow](#)
[2, 3 and 5 Way Manifolds](#)
[Metering Valves](#)
[Needle, Shutoff and Regulating](#)
[Quarter-Turn Plug](#)
[Relief](#)
[Sample Stream Select Actuated](#)
[Valve Locks](#)



SWAGELOK CUSTOM SOLUTIONS

[CAD Drawing of fabrications](#)
[Instrument Enclosures](#)
[Panels](#)
[Subassemblies](#)
[Specialized Tube Bending](#)
[Spool Pieces](#)
[Section IX Weld Certified](#)



SERVICE CAPABILITIES

[eBusiness Solutions](#)
[Quoting/Ordering Online](#)
[Pricing and Technical Support](#)
[2D and 3D CAD/Sales Drawings](#)



Helium Leak Testing MRO and Project Consignment Swagelok Energy Advisors

[Project Management](#)
[Steam and Compressed Air Audits](#)
[Steam System Engineering](#)
[Training](#)



Training and Education

[Orbital Weld Training](#)
[Swagelok University Online](#)
[Tube Bending](#)
[Tube Fitting Installation and Safety](#)
[Valve Selection](#)

Vendor Managed Inventory

NON-SWAGELOK PRODUCTS

[Push To Connect Fittings](#)
[Strut Framing Systems](#)
[Utility Ball Valves](#)
[SS Flanges & Fittings](#)

****Materials available include: Stainless Steel, Brass, Special Alloys, PTFE and Nylon. Fractional and metric sizes also available.****

Visit www.swagelok.com for our full catalog and pricing or contact one of our offices below.



North Carolina | East Tennessee

Raleigh, North Carolina
919.878.8085 Office
info@nctn.swagelok.com
<http://nctn.swagelok.com>

Charlotte, North Carolina
704.289.7400 Office
info@nctn.swagelok.com
<http://nctn.swagelok.com>

Knoxville, Tennessee
865.673.6610 Office
info@nctn.swagelok.com
<http://nctn.swagelok.com>

